

## Lindberg/Blue M Mini-Mate Tube Furnace (TF55030A)



### RENTAL AND APPLICATION NOTES:

- Shipping Weight: 28 lbs.
- This configuration can be used for US EPA method 16A & 16B for total reduced sulfur emissions.
- The microprocessor-based self-tuning PID (proportional, integral, derivative) control provides optimum thermal process without overshoot.

### SPECIFICATIONS:

- Weight: 28 lbs.
- Dimensions: 11" x 16" x 15".
- Chamber Dimensions: 1" diameter x 12" length.
- Power: 120V, 50/60 Hz, 800w.
- Temperature: Adjustable up to 1,100°C.
- Segment Control: 1 segment.
- K-type thermocouple.
- LED display has readings for actual temperature (in °F or °C) and set point.
- Low thermal mass Moldatherm® insulation.